




Pioneering the door to the future with commitment to technology

## The 4-Blades Slit with XZ <GHM-12XZ>

This is XY-stage which has 4-blades motorized slit. You can move to anywhere you like with keeping the aperture size.



< Shaping a beam in front of sample. KSU-10 >



## **Specifications**

Model	GHM-12XZ
Feature	Coupled Blades
Aperture Size	Maximum 15mm x 15mm
Blade Travel	0 - +7.5 mm (Each Blade)
Resolution (half-step)	0.5 $\mu$ m/ step (Each Blade)
Blade Material	Tantalum 5mm t
Dimension	117 x 119.5 x 46.6 mm³
Model	ZA05A-X1, XA05A-R1
Stroke	±7.5 mm

## **Features**

♦ GHM-12

Kohzu's Smallest 4-Blades Slit

1 Motor for 2 Blades.

◆2 blades are closed and opened at the same time.

♦ 50um cross-over when both blades completely shut.

◆ The Blade's parallelism and orthogonality are adjusted within 10 um by a Kohzu's technician for each by each.

The blade is made of Tantalum and precisely polished.

Option : The BISP type

(Blades In-the Same Plane) The smallest aperture is set for 20 um.

## ♦XZ stages

ZA05A-X1
XA05A-R1

Kohzu Precision Co.,Ltd. Tel: +81-44-981-2131 Fax: +81-44-981-2181 Email:sale@kohzu.co.jp URL://www.kohzuprecision.com